

# DATASHEET F-201AV

## EL-FLOW Select F-201AV

Digital Thermal Mass Flow Controller for Gases



### Gas Mass Flow Controllers for low/medium flow rates

Bronkhorst® model F-201AV Mass Flow Controllers (MFCs) are suited for accurate measurement and control of flow ranges between 0,4...20 l<sub>n</sub>/min and 2...100 l<sub>n</sub>/min at operating pressures between vacuum and 64 bar. The MFC consists of a thermal mass flow sensor, a precise control valve and a microprocessor based pc-board with signal and fieldbus conversion. As a function of a setpoint value, the flow controller swiftly adjusts the desired flow rate.

EL-FLOW® Select series are equipped with a digital pc-board, offering high accuracy, excellent temperature stability and fast response. The main digital pc-board contains all of the general functions needed for measurement and control. In addition to the standard RS232 output the instruments also offer analog I/O. As an option, an on-board interface can be mounted to provide CANopen®, DeviceNet™, EtherCAT®, PROFIBUS DP, PROFINET, Modbus RTU, ASCII or TCP/IP, EtherNet/IP, POWERLINK or FLOW-BUS protocols. The EL-FLOW® Select design features optional Multi Gas / Multi Range functionality, providing (OEM-) customers with optimal flexibility and process efficiency.

### Technical specifications

#### Measurement / control system

Flow range (intermediate ranges available)	min. 0,4...20 l <sub>n</sub> /min max. 2...100 l <sub>n</sub> /min (based on N <sub>2</sub> )
Accuracy (incl. linearity) (based on actual calibration)	± 0,5 % RD plus ±0,1% FS
Repeatability	< 0,2 % RD
Turndown ratio	up to 1:187,5 (1:50 in analog mode)
Multi fluid capability	storage of max. 8 calibration curves; optional Multi Gas / Multi Range functionality up to 10 bar abs
Settling time (in control, typical)	standard: 1...2 seconds option: down to 500 msec
Control stability	< ± 0,1 % FS
Operating temperature	-10 ... +70 °C
Temperature sensitivity	zero: < 0,05% FS/°C; span: < 0,05% Rd/°C
Pressure sensitivity	< 0,1% Rd/bar typical N <sub>2</sub> ; 0,01% Rd/bar typical H <sub>2</sub>
Max. Kv-value	6,6 x 10 <sup>-2</sup>
Leak integrity, outboard	up to 1:187,5 (1:50 in analog mode)
Attitude sensitivity	max. error at 90° off horizontal 0,2% at 1 bar, typical N <sub>2</sub>
Warm-up time	30 min. for optimum accuracy 2 min. for accuracy ± 2% FS

Mechanical parts

Material (wetted parts)	Stainless steel 316L or comparable			
Pressure rating (PN)	64 bar abs			
Process connections	compression type or face seal (VCR/VCO) couplings			
Seals	standard: Viton®; options: EPDM, Kalrez® (FFKM), FDA and USP Class VI approved compounds			
Weight	0,7 kg			
Ingress protection	IP40			

Electrical properties

Power supply	+15 ... 24 Vdc			
Max. power consumption	Supply	at voltage I/O	at current I/O	extra for fieldbus
	15 V	290 mA	320 mA	<75 mA
	24 V	200 mA	215 mA	<50 mA
Analog output	0...5 (10) Vdc or 0 (4)...20 mA (sourcing output)			
Digital communication	standard: RS232; options: PROFIBUS DP, CANopen®, DeviceNet™, PROFINET, EtherCAT®, Modbus RTU, ASCII or TCP/IP, EtherNet/IP, POWERLINK, FLOW-BUS			

Electrical connection

Analog/RS232	9-pin D-connector (male);
PROFIBUS DP	bus: 9-pin D-connector (female); power: 9-pin D-connector (male);
CANopen® / DeviceNet™	5-pin M12-connector (male);
FLOW-BUS/Modbus-RTU/ASCII	RJ45 modular jack
Modbus TCP / EtherNet/IP / POWERLINK	2 x RJ45 modular jack (in/out);
EtherCAT®/ PROFINET	2 x RJ45 modular jack (in/out)

Control valve options

External actuator options to be connected to the controller

Ex-proof specifications

Approvals / certificates

Technical specifications subject to change without notice.

For dimensional drawings and hook-up diagrams please visit the [product page](#) on our [website](#)

Recommended accessories



E-8000 SERIES

Digital Readout / Control Systems

Bright, wide angle, 1.8" display (TFT technology)  
User friendly operation, menu driven with 4 push buttons



BRIGHT SERIES

Compact Local R/C Module

Bright, wide angle, 1.8" display  
User friendly operation  
Indication/operation/configuration



PIPS SERIES

Plug-in Power Supply

For lab-style or industrial devices  
Interchangeable plugs (Euro, UK, USA, Australian, IEC) for mains connection



IN-LINE FILTER  
SERIE M-411 RS

1/4" female in / male out  
100 bar  
Average porosity 0.5...15 µm

Related products



EL-FLOW SELECT F-201CV

Min. flow 0,16...8 ml/min  
Max. flow 0,5...25 l/min  
Pressure rating 64 bar  
Compact design  
High accuracy and repeatability



EL-FLOW SELECT F-211AV

Min. flow 0,4...20 l/min  
Max. flow 2...100 l/min  
Pressure rating 100 bar  
Compact design  
High accuracy and repeatability



EL-FLOW SELECT F-202AV

Min. flow 0,8...40 l/min  
Max. flow 5...250 l/min  
Pressure rating 64 bar  
Compact design  
High accuracy and repeatability



EL-FLOW SELECT F-111AC

Min. flow 0,4...20 l/min  
Max. flow 0,6...100 l/min  
Pressure rating 100 bar  
Compact design  
High accuracy



**BRONKHORST USA LLC**

57 South Commerce Way

Suite 120

USA - Bethlehem, PA 18017

Tel. +1-610-866-6750

[sales@bronkhorstusa.com](mailto:sales@bronkhorstusa.com)

